


Guidance sheet (please see test data sheet for further information)

## Material ref AR990 'Self Apply' Self Adhesive Backing

High tack, hot melt adhesive tape, covered with a white silicone release paper.  
Available in 50 metre coils in a range of widths.



For use as a economical temporary fixing to hold solid rubber, cork or foam gasket strip in position when assembling. Simply peel from roll, place directly on rubber strip and rub down, pull off silicone paper and place gasket in position. In the case of 'self apply' we recommend adhesive tape to be narrower than rubber gasket, example 15mm or 19mm wide to suit 25mm wide rubber strip.  
In the case of solid rubbers we do not recommend the adhesives long term performance as a stand alone fixing.

Also supplied in strip form already laminated to -  
Material ref AR110, Black Closed Cell Neoprene Sponge  
Material ref AR120, Black Closed Cell EPDM Sponge  
Material ref AR122, (off) White Closed Cell EPDM Sponge  
Material ref AR428, Black Solid Commercial Neoprene

### Delivery

95% of products are despatched within 24hours of receiving order (exception: self adhesive solid neoprene strip, 3 to 5 working days). If orders are required by a specific deadline please email or phone prior placing your order for definite delivery date.

Material samples are available by request and specific questions can be asked via email:

[sales@rubberonlinelimited.co.uk](mailto:sales@rubberonlinelimited.co.uk)

The above is a rough guide and is subject to change without notice.

This information is designed to guide you, the customer, to the most suitable product for your intended application.

The assessment of use is the responsibility of the customer and any liability will remain with the customer.

Terms and conditions apply.

We are committed to customer satisfaction, if you have any concerns about our products or service please contact on us 01268 732185 and ask for customer services.